

Project Name

Location

Prepared By



SATCO S11472

8.5BR30/LED/840/120V/6PK

Notes

[www] 11-21-2022 00:39:09

General

Status	Active
Watts	8.5W
Incandescent Equivalent	65W
Volts	120V
Shape	BR30
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	80
Lumens	700L
Beam Spread	100
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Reflector
Technology	LED

Electrical

Operating Frequency	60 Hz
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	5.13
MOD	3.75
Lensed	Lensed Lamp
Lens Finish	Frost
Weight (lb.)	0.20

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus Listed
Location Rating	Damp
Energy Star	Pending
RoHS Compliant	Yes
SDS Sheet	LED_Lamp