










PROLINE G2




1  (1x)	2 M6X16  (8x)
3 M6  (8x)	4  (1x)


4




1




8X



2




13.6 ± 1.4 N*M
[120 ± 12.0 LBF*IN]



8X

3





HOFFMAN



HOFFMAN