










HOFFMAN


PROLINE G2



1  (3x)	2  (3x)	3  (3x)
4  (3x)	5 M6X16  5.1 ± 0.5 N·m [45 ± 4.5 LBF-IN] (6x)	6  (3x)
7  (1x)		





1




3X


7




2




3X




3








3X



4



5



1

