

DALS LIGHTING

NOTES:

Canada 80, de la Seigneurie blvd., E. Blainville, Quebec J7C 4N1

U.S.A. 4383, NW 124th Ave., Coral Springs, Florida 33065 877.430.1818 info@dals.com dals.com

MODEL NAME


DRR4-CC-V NOTCH

4-Inch Regressed Panel Light


downlights is characterized by a deepset LED position which greatly reduces glare, neatly packaged in a priceconscious solution to general lighting.







		DELIVERED	COLOR °T			BEAM	
SIZE	WATTS	LUMENS*	5CCT	CRI	VOLTAGE	ANGLE	FINISH
4"	11W	800lm	2700K	90	120-277V	100°	○ White
			3000K				<u> </u>
			3500K				
			4000K				
*Lumen output measured at 3000K			5000K				



CONSTRUCTION	Lens Frosted	Type of optics Acrylic	Type of LED SMD	
	Lens material Plastic	Housing material Cast aluminum	Cut hole size 4-1/4"	
RATINGS	Placement Indoor/Outdoor	Lifespan 50,000 hrs.	FT rating	
	Location Wet	Certifications ETL, FCC, ICES, ES IC ASTM F283-04 T24	Operating temperature -20° to 40° C	

WHAT'S IN THE BOX

ALUCY CDECC

LED recessed fixture Junction box Push-in wire connectors Mounting hardware Instruction sheet

ACCESSORIES

RFP-UNI Universal Drilling Plate

RFP-46 **Drilling Plate**

DRR4-TRIM-BK

Panel Trim in Black DRRP4-TRIM-SBA

Panel Trim in Sandblasted Aluminum

ADAPTERS

REC-EXT108

108" extension cord for recessed fixtures

REC-EXT230

230" extension cord for recessed fixtures



Canada

80, de la Seigneurie blvd., E. Blainville, Quebec J7C 4N1

U.S.A. 4383, NW 124th Ave., Coral Springs, Florida 33065

877.430.1818 info@dals.com dals.com

ELECTRICAL DETAILS

Input voltage 120-277V

Output current 251mA

Power factor

Driver type Constant current

Output voltage

34V

LED model # 2835

THD harmonic distortion <30%

Binning type 3,4 SDCM

FEATURES

Every fixture includes a junction box with an integrated driver

Superior LED performance and lifespan

Minimal heat emission

Switch-selectable CCT: 2700K/ 3000 K/ 3500 K/ 4000 K/ 5000 K

Can be daisy chained

Smooth 360° wide spread

Back-lit technology

Frosted lens

0-10V dimming

WARRANTY

DALS offers a 5-year warranty from the date of purchase which covers repairs or replacement of defective parts of the housing, optics, and electronics. To contact DALS customer service call 1-877-430-1818 or send an e-mail to info@dals.com.

RECOMMENDED DIMMER LIST*

DIMMING MAX **BRAND** MODEL# **DIMMER SPECS GRADE** RANGE (%) LOAD

DVSTV (0-10 V Controls) Lutron

960W, Operating Voltage: $120-277 V \sim$, Load Switching Capacity: 8 A

Compatible

^{*} Minimal buzzing noise may occur with some dimmers