



H40 Series

200 AMP - MULTI POSITION 400 Amp Main

CATALOGUE #	TYPE	DESCRIPTION	DIMENSIONS (IN.)			WEIGHT
			H	W	D	
H42R	O/H & U/G	2 gang, 400 Amp main, 200 Amp per position	22 ¹³ / ₁₆	18 ⁹ / ₁₆	6 ¹ / ₈	42 lbs.
H43R	O/H & U/G	3 gang, 400 Amp main, 200 Amp per position	22 ¹³ / ₁₆	27 ¹³ / ₁₆	6 ¹ / ₈	58 lbs.
H44R	O/H & U/G	4 gang, 400 Amp main, 200 Amp per position	22 ¹³ / ₁₆	37 ¹ / ₁₆	6 ¹ / ₈	74 lbs.
H45R	O/H & U/G	5 gang, 400 Amp main, 200 Amp per position	22 ¹³ / ₁₆	46 ⁵ / ₁₆	6 ¹ / ₈	87 lbs.
H46R	O/H & U/G	6 gang, 400 Amp main, 200 Amp per position	22 ¹³ / ₁₆	55 ⁹ / ₁₆	6 ¹ / ₈	104 lbs.

- Double entrance holes (top)
- Factory bussed 400 Amp Mains
- 200 Amp, 600 VOLT per position
- 2 - 6 position horizontal
- 4 Jaw meter sockets
- CSA weatherproof enclosure 3R
- Approved conductor range:
Line 1 - No. 2 - 600 MCM CU/AL
or Two - 1/0 - 250 MCM CU/AL
Load No. 6 - 250 MCM CU/AL

- For overhead order **HD** Series hub separate
- Add suffix "H" for right hand entry
- Approved for overhead and underground installations
- Use **SXK503** for 5th jaw at 9 O'clock
- Use **SXC022** for water heater lug kit

KNOCKOUT CODE	CONDUIT SIZE
G	1 ¹ / ₄ ", 1 ¹ / ₂ ", 2", 2 ¹ / ₂ "
S	3", 3 ¹ / ₂ ", 4"
AA	1 ¹ / ₂ "

