

# Eaton NZMB2-AF200-BT-NA

Catalog Number: NZMB2-AF200-BT-NA

MCCB NZM, NZM2 TM and Elec. Breakers, Circuit Breaker, 200-200A OL Prot. Rng, Frame clamp, front, Three-pole, 200A Perm. Current, 25 kA, 200-200A Set. Rng OL Prot., 1200-2000A Undelayed Adj. Rng., Rocker lever, motor drive optional

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Series NZM complete molded case circuit breaker	NZMB2-AF200-BT-NA
	<b>EAN</b>
	4015081072941
<b>Product Length/Depth</b>	<b>Product Height</b>
5.51 in	5.86 in
<b>Product Width</b>	<b>Product Weight</b>
5.86 in	5.17 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	



## Product specifications

### Interrupt rating

25 kAIC

### Frame

NZM2

### Overload range

200-200A

### Setting Range OI Protector

200-200A

### Connection

Front frame clamp

### Short-circuit breaking capacity

25 kAIC

### Amperage Rating

200 A

### Number of poles

Three-pole

### Accessories

Rocker lever, motor drive

### Adjustment range short-circuit release

1200-2000A delayed

### Circuit breaker type

NZMB2

### Class

Distribution circuit protection

### Terminals

Box

### Voltage rating

440 Vac

### Trip Type

Fixed thermal, adjustable magnetic

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - NZMB2-AF200-BT-NA](#)

[Product Data Sheet - NZMB2-AF200-BT-NA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)