

Eaton C25ANB130B

Catalog Number: C25ANB130B

Eaton definite purpose contactor, Quick, 30A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, Compact, single-pole, 30A, Contactor, Single-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing

General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25ANB130B
UPC	Product Length/Depth
786685115863	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
.5 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified UL Recognized



Product specifications

Frame size

Compact, single-pole

Type

Non-reversing

Inductive full load

30 A

Model

Contactors

Connection

Quick

Enclosure

Open with metal mounting plate

Terminals

Binding head screw and quick connect terminals (side-by-side)

Amperage Rating

30A

Resistive load

40 A

Number Of Poles

Single-pole

Coil

208-240 Vac, 50/60 Hz

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25ANB 2D Drawing Xchange](#)

[C25ANB 2D PDF](#)

[C25ANB AutoCAD 2D Footprint \(mm\)](#)

[C25ANB 3D Model Xchange](#)

[C25ANB AutoCAD 2D Footprint](#)

[C25ANB 3D Inventor](#)

Specifications and datasheets

[Quick Selector - Definite Purpose Contactors](#)

[Eaton Specification Sheet - C25ANB130B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)