

Eaton M22-LEDC-G

Catalog Number: M22-LEDC-G

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 100, Illuminated, Green, 12-30 Vac/dc

General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-LEDC-G
UPC	Product Length/Depth
786685277707	1 in
Product Height	Product Width
.25 in	.9 in
Product Weight	Warranty
.1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked GoST-R Bureau Veritas	CCC Marked CSA Certified Lloyd's Register Certified



Product specifications

Light color

Green

Series

M22

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 100

Illumination

Illuminated

Size

22.5 mm

Voltage rating

12-30 Vac/dc

Actuator

Base, screw

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-LEDC-G](#)

[Global Data Sheet - M22-LEDC-G](#)

[Quick Selector - M22 Pushbuttons](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)