


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FULLY ROUNDED  
EDGES ALONG  
STRAP BODY

SECTION A - A  
SCALE 6:1

NOTES:

1. APPLICATION TOOLS - GS4MT-E, PPTMT, ST2MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 450 LBS (2000 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [ ] DENOTES DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
 .XXX = ±.010 [ .25]    .XX = ±.020 [ .5 ]  
 .X = ±.030 [ .8]    ANGLES = ±2°
5. MATERIAL: 316 STAINLESS STEEL

PANDUIT PART NO.	PACKAGE QTY	MAX BUNDLE DIAMETER	LENGTH "L" ±.3 [ 7 ]
MLT2H-LP316	50	2" [ 51 ]	7.9" [ 201 ]
MLT2.7H-LP316	50	2.7" [ 69 ]	10.2" [ 259 ]
MLT4H-LP316	50	4" [ 102 ]	14.3" [ 362 ]
MLT6H-LP316	50	6" [ 152 ]	20.5" [ 521 ]
MLT8H-LP316	50	8" [ 203 ]	26.8" [ 679 ]
MLT10H-LP316	50	10" [ 254 ]	33.0" [ 838 ]
MLT2H-TL316	250	2" [ 51 ]	7.9" [ 201 ]
MLT4H-TL316	250	4" [ 102 ]	14.3" [ 362 ]

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
08A	01-20-23	JBN	JADE	MRWA	UPDATED TOOL LIST: CHANGED GS4MT TO GS4MT-E & REMOVED ST3MT UPDATED DRAWING TYPE TO CUSTOMER INSTEAD CONTROL	128498/00
07A	02-20-15	BDK	SKB	RGRO	UPDATED TITLE BLOCK AND BORDER	N41116BS_DC

TITLE <b>METAL LOCKING TIE - HEAVY SERIES 316 STAINLESS STEEL</b>				CUSTOMER DRAWING	
ITEM REVISION NAME N41116BS/08				<b>PANDUIT</b>	
DATASET FILE NAME N41116BS_DC/08A					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]				MATERIAL: 316 STAINLESS STEEL	
.X ± .1 [ 2.54 ]		.XXX ± .005 [ .127 ]		DRAWING NUMBER: N41116BS_DC	
.XX ± .01 [ .25 ]		ANGLES ± 5 °		THIRD ANGLE PROJECTION	
DRAWN BY JAMB	DATE 2/12	CHK DPN	SCALE 2:1	SHT 1 OF 1	
				SIZE A	

D10100DA/16