










HOFFMAN

PROLINE G2




1  (4x)	2 M5X10  (16x)	3 M6  (8x)
4  (8x)	5 M6X16  (8x)	






5.1 ± 0.5 N*M
[45 ± 4.5 LBF-IN]



8X

2



3