

















HOFFMAN


PROLINE G2




1  (8x)	2  (8x)	3  (8x)
4  (2x)	5  (4x)	6 M10X1.5X16; 12X12 SHLDR  (2x)
7  (1x)	8  (2x)	9  (1x)
10  (2x)	11  (1x)	12  (2x)






1




2.1.a




2.1.b




2.2.a





2.2.b




2.2.c




3.a






3b




3c




3d



3.4 NM $\pm$ 0.3
[30 LB IN $\pm$ 3.0]



3e



W	D mm [in.]	
	A	B1, B2
600	170 [6.7]	210 [8.3]
800	320 [12.6]	495 [19.5]



HOFFMAN



HOFFMAN