











HOFFMAN


PROLINE G2




1  (1x)	2  (2x)	3  (2x)
4 M4X8  (10x)	5  (4x)	6  (4x)
7  (4x)		




4X




1




2.4 ± 3.0 N*M
[21 ± 2.1 LBF-IN]



2X



3



4



HOFFMAN