WIDE WIRE RANGE COMPACT SIZE | ERGONOMIC WING DESIGN | FLEXIBLE SKIRT WISTER® PROFLEX® MINI
WIRE CONNECTORS CHAMPION TO THE ELECTRICIAN'S

TWISTER® PROFLEX™ MINI WIRE CONNECTORS

FLEXIBLE SKIRT FOR ADDED PROTECTION

The Twister® ProFLEX™ Mini boasts a space-saving design that fits into the tightest electrical spaces, with the added protection of a flexible skirt.

It features the widest wire range of any orange/blue connector. Can be used for combinations from 2 #22 AWG to 4 #12 solid AWG wire.

RATED 4 #12 **SOLID**

Expanding square-wire spring and polypropylene shell deliver a secure connection every time

> Tough, UL 94V-2 flame-retardant shell

with SureGrip™ overmold offers greater comfort. leverage, and torque for faster connections Flexible skirt provides improved protection and adapts to tightly fit electrical boxes with limited space

Model	Colour	Wire Combination Range	Wire Combination Range (mm)	Quantity	Part No.
343	Orange/ Blue	600V* 22 to 12 AWG Min. 2 #22 - Max. 4 #12 Sol. WIDEST RANGE of any orange/blue connector!	600V* .34mm² to 4.0mm² Min. 2 .34mm² Max. 4 4.0mm²	Box of 100	30-343
				Jar of 500	30-643J
				Barrel of 35,000	30-843

*1,000V maximum in fixtures and signs.

Swept wing design



IDEAL CUSTOMER SERVICE: orderdesk@idealindustries.com 1-800-824-3325 www.idealind.com

©2021 IDEAL INDUSTRIES, INC.



