Duo-puck









These robust LED pucks, featuring a frosted lens, deliver highly efficient punches of white light. Well suited for under-cabinet lighting and a variety of other applications.



Model	Size	Watts	Delivered lumens	CRI	Color °T	Voltage
4005-CC	Ø2.625"	2 W	138 lm	80	2700, 3000, 3500,	12 V
K4005-CC	Ø2.625"	2 W*	138 lm*	80	4000, 5000 K	

^{*}Per fixture

Specifications

12V DC LED driver required
Over 50,000 hours of service life
12" input lead with quick connector
24" interconnection harness included
Can be recessed or surface mounted
Switch-selectable CCT: 2700 K/3000 K/
3500 K/4000 K/5000 K

Excellent color rendering
Superior LED performance and lifespan

Smooth 360° wide spread

Minimal heat emission

Steel/aluminum construction

Frosted glass lens

Kits available

Refer to website for dimmer compatibility 5-year warranty

Note

Plug-in or hard-wired power supply required for installation. Sold separately.

Other color °T and finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

Finish

BK Black

SN Satin Nickel

WH White

Power supplies: plug-in

ETR-LED10WPI

12V DC/10W class 2 LED driver

ETR-LED24WPI

12V DC/24W class 2 LED driver

Power supplies: hard-wired

BT06DIM-IC

6W dimmable LED hardwire driver

BT12DIM-IC

12W dimmable LED hardwire driver

BT24DIM-IC

24W dimmable LED hardwire driver

BT36DIM

36W dimmable LED hardwire driver

BT48DIM

48W dimmable LED hardwire driver

Accessories

4000-E24

24" extension cord

4000-E60

60" extension cord

4000HRNS-24

24" interconnection harness



