

Eaton TRAFGF20W

Catalog Number: TRAFGF20W

Eaton AFGF receptacle, Tamper resistant, Self-test, #14 - 10 AWG, 20A, Residential, Commercial, Flush, 125 V, AFGF, Back and side wire, White, Brass, Receptacle, Tamper resistant, Polycarbonate, 5-20R, Two-pole, three-wire, grounding

General specifications

Product Name	Catalog Number
Eaton AFGF receptacle	TRAFGF20W
UPC	Product Length/Depth
032664747700	2.815 in
Product Height	Product Width
4.625 in	2.01 in
Product Weight	Warranty
.401 lb	Refer to warranty document.

Certifications

CSA Certified cULus Listed UL Listed
NOM



Product specifications

Circuit interrupter type

AFGF

Device type

Receptacle

Color

White

Face/body material

PVC

Polycarbonate

Wiring method

Back and side wire

Features

Tamper resistant

Mounting method

Flush

Allowable wire size

#14 - 10 AWG

Amperage Rating

20 A

Contact material

Brass

Type

Self-test

NEMA configuration

5-20R

Environmental conditions

Tamper resistant

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125V

Application

Residential

Commercial

Torque rating

Resources

Brochures

[AF/GF dual-purpose receptacles sell sheet](#)

Installation instructions

[Installing and testing an AF/GF receptacle](#)

Multimedia

[Ground Fault Circuit Interrupter \(GFCI\) demonstration](#)

Specifications and datasheets

[AF/GF duplex receptacle spec sheet](#)

16 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)