| Project | | |
|---------|--|--|
| , | | |
| 0-4-1 | | |

Type _____



CSRM1STEEL COMBO RUNNING MAN

The CSRM1 series is our entry-level combination sign. Two PAR18 small style, front mounted heads are standard and complete the unit.

FEATURES & SPECIFICATIONS

ELECTRICAL CIRCUITRY

- · 120-347 VAC Input
- 6 VDC emergency power output
- · Wattage capacities 27 W
- 120 minutes emergency power duration as a standalone unit
- Momentary push button test switch
- Pilot LEDs for AC, ON and CHARGE
- Fully automatic, current limiter charger
- Maintenance free, sealed lead acid battery

MECHANICAL

- · 20 Gauge steel construction
- Universal spider knockout pattern stamped into backplate for junction box mounting
- Universal models include ceiling or end mount, field installable canopy kit c/w spider plate
- White powder coat finish standard

APPROVALS

 CSA Certified to C22.2 #141-15

COMPLIANCE

 Meets requirement of ICES-005

| OVERVIEW | | | |
|-------------------------------------|---------------|----------------------|---------|
| LIGHT SOURCE | LED | INPUT VOLTAGE (V CA) | 120-347 |
| SIGN EMERGENCY POWER CONSUMPTION | 6 VDC = 0.9 W | OUTPUT CAPACITY (W) | 27 |
| | | | |



QUICKSHI





POWER CONSUMPTION TABLE

| MODEL | VOLTAGE | POWER | CURRENT |
|-------|---------|-------|---------|
| | 120 V | 3.2 W | 0.03 A |
| CSRM1 | 277 V | 3.4 W | 0.014 A |
| | 347 V | 3.6 W | 0.01 A |

For complete warranty details, please see our terms and conditions on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.



TF 1866 348-2374

QUICK SHIP ORDERING GUIDE



| PART | DC | WATTS | NBR OF | NBR OF | HEAD | LAMP | LIGHT | INPUT | COLOR |
|--------|-------|-------|-----------|--------|------|------|--------|---------|-------|
| NUMBER | VOLTS | | FACES | HEADS | | | SOURCE | VOLTS | |
| | (VDC) | (W) | | | | (W) | | (VAC) | |
| CSRM1 | 6 | 27 | UNIVERSAL | 2 | N | 2 | LED | 120-347 | WHITE |

QUICK SHIP: Product availability is subject to change without notice. Please contact your AimLite customer service representative to confirm inventory levels at time of order.

MODEL RATINGS

| MODEL | | WATTAGE CAPACITIES [W] | | | | |
|-------|-----------|------------------------|--------|--------|---------|--|
| MUDEL | VOLTS (V) | 30 MIN | 60 MIN | 90 MIN | 120 MIN | |
| CSRM1 | 6 | 27 | 14 | 9 | 7 | |


ACCESSORIES (ORDER SEPARATELY)


| PART NUMBER | TYPE |
|-------------|----------------------------|
| FIBER-RPSC | RUNNING MAN FIBER NO ARROW |

WIREGUARD1

| | PART NUMBER | DIMENSIONS |
|---------------|-------------|-------------------------|
| WALL MOUNT | WGD510 | 17.25" X 17.25" X 7" |
| CEILING MOUNT | WGD650 | 13.75" X 12.25" X 16.5" |
| END MOUNT | WGD650 | 13.75" X 12.25" X 16.5" |

¹Please contact your Stanpro customer service representative for more information.





CONFIGURATIONS

ends for direction selection.





please order the RPNP along with the following fiber: FIBER-RPSC.

