

Project Name

Location

Prepared By



NUVO 65-550

LED ADJUSTABLE VAPOR TIGHT

Notes

[www] 05-23-2020 01:02:33

General

Status	Active
Fixture Type	Vapor Proof
Finish	Gray
Wattage	20W
Lumen Output	1700L-2000L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
Color Temperature	Warm to Cool White
CRI	80
Voltage	120V-277V
Beam Angle	210
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
Dimmable	Non-Dimmable
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	4.19
Material	Die Cast Aluminum

Dimensions

Height (in.)	13.19
Width (in.)	4.72
Extension (in.)	7.09

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2394485
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------