

Project Name

Location

Prepared By



SATCO S11446

12A19/PIR/950/120V/ND

Notes

[www] 05-08-2023 01:24:11

General

Status	Active
Watts	12W
Incandescent Equivalent	75W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90
Lumens	1050L
Beam Spread	230
Dimmable	Non-Dimmable
Hours Rated	15000
Photocell or Sensor	Has PIR Sensor
Technology	LED

Electrical

Operating Frequency	60Hz
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	5.11
MOD	2.36
Weight (lb.)	0.27

Additional Information

Specification Note	Dual Mode Capable: Motion or On-Off Switch
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes