

FM70-LED

Flush mount



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

WIRING:	Installs easily in traditional junction boxes.
HOUSING DETAILS:	This flush mount unit uses metal housing. The Apollo Series is available with or without the motion sensor. The motion sensor is a PIR sensor, with a detection range of 3' (1M) to 6' (2M) and a time delay of 5 minutes. Sensing no movement within that time period, the unit will shut off automatically.
OPTICS:	LED technology delivers 1000 lumens.
ELECTRICAL:	Easily connected to a 120V power supply via provided UL recognized driver. DAMP LOCATIONS and DIMMABLE. Motion sensor model is non-dimmable. Dimming down to 10% with most standard LED dimmers (see list of approved products). Certified for use in closets. * Certifications: This product is ETL and Energy Star listed in USA & Canada. **Meets NFPA70, NEC 410.16, C(1) requirements."
LENS:	White decorative acrylic frosted lens provides an even light distribution.

COLOR TEMPERATURE:	3K - 4K
OPERATING TEMPERATURE:	-20°C + 40°C
CRI:	90+
LUMEN OUTPUT:	1000 lumens
DIMMABLE:	Yes
WATTS:	13W
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120V
DIAMETER:	7.13" (181mm)
HEIGHT:	1.3" (33.5mm)
INTEGRATED MOTION SENSOR:	No

APPLICATIONS

FM70-LED

Flush mount

DIMENSIONS



RATINGS



ORDERING GUIDE

APOLLO FM70 SERIES

Series	Color Temperature	Finish
FM70-0510	3K 3000K/90CRI/13W 4K 4000K/90CRI/13W	WH White

Notes: Configure product using **BOLD** options: Ex: **FM70-0510-3K-WH**