

TECHNICAL DATA

Fluke TL75 Hard Point™ Test Lead Set



Key features

- Test lead and probe in one unit
- 48 inches (1.22 meter) long
- CAT II 1000 V, 10 A rated
- CAT IV 600 V, CAT III 1000 V rated with protective cap
- CSA Listed

Product overview: Fluke TL75 Hard Point™ Test Lead Set

Product overview: Fluke TL75 Hard Point™ Test Lead Set

The Fluke TL75 Hard Point™ Test Leads are a set of comfort grip, PVC-insulated probes. TL75s offer the convenience of a test lead and probe together in one unit with a variety of connections. This set of test leads are recommended for all general-purpose measurements and are compatible with a wide range of Fluke meters and tools.

Designed for safety

The Fluke TL75 Hard Point™ Test Lead Set is CAT II 1000 V, 10 A rated. When the protective caps are placed on the leads, the ratings jump up to CAT IV 600 V, CAT III 1000 V.

Compatible with Fluke alligator clips

Expand your measurement capabilities with special adapters to your TL75 set. Add alligator clips or adapters to accomplish even more:

- [Fluke AC175 Alligator Clip Set](#)
- [TP920 Test Probe Adapter Set](#)

Ordering information



Fluke TL75 Hard Point™ Test Lead Set

- One pair (red, black) of comfort grip probes
- 48 inches (1.22 meter) PVC insulated test leads with right-angle shrouded banana plugs



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2023 Fluke Corporation.
Specifications subject to change without notice.
05/2023

**Modification of this document is not permitted
without written permission from Fluke Corporation.**