Spot

This durable, fully sealed 12V LED landscape spot is constructed of solid aluminum. It includes an integrated LED module that emits a cool, natural, or warm white light in multiple beam patterns, all selectable with a 5CCT switch. Can be rotated 180° and equipped with a glare shield for pinpoint accuracy. The landscape spotlight is great for gardens, tree uplighting, architectural lighting, and more.













Model	Size	Watts	Delivered lumens	CRI	Color °T	Voltage	
LSP3-CCL	3"	10 W	500 lm	80	2200, 2700, 3000,	12 VAC	
LSP4-CCL	4"	20 W	1000 lm		3500, 4000 K		

Specifications

Over 50,000 hours of service life

12VAC input

Switch-selectable CCT: 2200 K/2700 K/ 3000 K/3500 K/4000 K

Easy-access CCT switch on back of spot

Interchangeable 20°, 40°, and 90° beam angle lens

180° swiveling head

Cast aluminum construction

Ground stake included

Suitable for wet locations

5-year warranty

Finish



BK Black

Power supplies

LTRP-60-BK

60W, 120VAC 60Hz input 12VAC output low-voltage transformer

LTR-300-BK

300W, 120VAC 60Hz input 12/13/14/15VAC output low-voltage transformer

Note

Low-voltage transformer required. Sold separately.

Other color °T and finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

Accessories

LAN-ACC-MS

6 ¾" metal ground stake

LSP-EXT04

4" extension arm

LSP-WM

Spotlight wall mount adapters

LCBL-50-16

50 feet of 16 gauge low-voltage wiring

LCBL-100-16

100 feet of 16 gauge low-voltage wiring

LCBL-50-14

50 feet of 14 gauge low-voltage wiring

LCBL-100-14

100 feet of 14 gauge low-voltage wiring

LCBL-100-12

100 feet of 12 gauge low-voltage wiring

LCBL-200-12

200 feet of 12 gauge low-voltage wiring





