



A-Shape LED

8.8A19/PER/930/P/E26/DIM 6/1FB T20

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data


General Information		Warm-up time to 60% light	
Cap-Base	E26 [Single Contact Medium Screw]		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)	0.7
Switching Cycle	50,000	Voltage (Nom)	120 V
Lighting Technology	LED	Temperature	
Light Technical		T-Case Maximum (Nom)	90 °C
Color Code	930 [CCT of 3000K]	Controls and Dimming	
Beam Angle (Nom)	250 degree(s)	Dimmable	Yes
Luminous Flux	800 lumen	Mechanical and Housing	
Color Designation	White (WH)	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	3000 K	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Shape	A19 [A 19mm]
Color Consistency	<4	Approval and Application	
Color rendering index (CRI)	90	Energy Consumption kWh/1000 h	- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Certifications	Energy Star
Operating and Electrical		EU RoHS compliant	Yes
Line Frequency	60 Hz	Product Data	
Input Frequency	60 Hz	Order product name	8.8A19/PER/930/P/E26/DIM 6/1FB T20
Power Consumption	8.8 W	Order code	550442
Lamp Current (Nom)	80 mA	Numerator - Quantity Per Pack	1
Wattage Equivalent	60 W		
Starting Time (Nom)	0.5 s		

A-Shape LED

Numerator - Packs per outer box	6
Material number (12NC)	929002036204
Full product name	8.8A19/PER/930/P/E26/DIM 6/1FB T20



EAN/UPC - Case	50046677550443
----------------	----------------

Dimensional drawing




Product	D	C
8.8A19/PER/930/P/E26/DIM 6/1FB T20	62.5 mm	111.5 mm

Photometric data



Light Distribution Diagram - 8.8A19/PER/930/P/E26/DIM 6/1FB T20



Spectral Power Distribution Colour - 8.8A19/PER/930/P/E26/DIM 6/1FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 8.8A19/PER/930/P/E26/DIM 6/1FB T20

Lumen Maintenance Diagram - 8.8A19/PER/930/P/E26/DIM 6/1FB T20

