



Ratchet Cable Cutter, Cuts up to 556 kcmil ACSR, 500 kcmil Aluminum, up to 500 kcmil Copper

By Burndy
Catalog # [RCC556](#)



Ratchet Cable Cutter, Cuts up to 556 kcmil ACSR, 500 kcmil AL, 500 kcmil CU.

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable
EU RoHS Indicator	Yes
Sub Brand	RATCHET CUTTER
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810174852
UPC 12 Digit	7818101748522

Dimensions

Cable Insulation Diameter Maximum	1.400 in
Height	5.5 in
Length	21 in
Weight	4 lb

Certifications and Compliance

Standards - RoHS Compliance Status EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Cutters \(2150\)](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE211273-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-RCC556-SPEC-EN | REV 5/2023