



# Ratchet Cable Cutter, Cuts up to 1000 kcmil Copper and Aluminum, Maximum Insulation Diameter 2.375"

By Burndy  
Catalog # [RCC1000](#)



Ratchet Cable Cutter, Cuts up to 1000 kcmil CU/AL, Max Ins Dia. 2.375".

### Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

### Application

Cutting

### General

Application - For Use On	Aluminum, Copper Cable
EU RoHS Indicator	Yes
Sub Brand	RATCHET CUTTER
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810174883
UPC 12 Digit	7818101748833

### Dimensions

Cable Insulation Diameter Maximum	2.375 in
Height	6 in
Length	20 in
Weight	4.5 lb

### Certifications and Compliance

Standards - RoHS Compliance EX  
Status

### Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

### Product Assets

[Catalogs - Cutters \(2150\)](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE211271-01](#)



A proud member of the Hubbell Family.