



Stainless Steel W Die, Index 162

By Burndy
Catalog # [W162](#)

W Die, Index 162.



Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	162
Die Type	W Die
EU RoHS Indicator	Yes
Sub Brand	W-DIE
Type	W-Die for Hydraulic Crimping Tools (set)
UPC	781810440261
UPC 12 Digit	7818104402611

Conductor Related

Crimping Ranges Aluminum: #4 AWG

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	80
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10102381](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-W162-SPEC-EN | REV 5/2023