



Stainless Steel W Die, Index O

By Burndy
Catalog # [WO](#)

W Die, Index O.



Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	O
Die Type	W Die
EU RoHS Indicator	Yes
Sub Brand	W-DIE
Type	W-Die for Hydraulic Crimping Tools (set)
UPC	781810440452
UPC 12 Digit	7818104404522

Conductor Related

Crimping Ranges

Copper: 14 Sol. - 350 kcmil;
AAC: 14 Sol. - 3/0 AWG;
ACSR: #2 AWG - 3/0 AWG

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	80
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50007852](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-WO-SPEC-EN | REV 5/2023