

HYTOOL™ Hand-Operated Crimper, Installs #14 - 4/0 AWG, Permanent BG (5/8) and D3 grooves

By Burndy Catalog # MD6

Crimper, Installs #14-4/0 AWG, BG & D3 Grooves.



Features

- Ergonomically designed, one-piece, composite polymer handles
- · Comfort grip handles
- Time-proven steel jaw designs
- · No tool adjustment required
- 99,000 crimp/cycle life
- · Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- · Electroless nickel plated jaws and jaw links

Application

Crimping

General

Application - For Use On Copper, Aluminum, ACSR,

Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact

Conductors

Crimp Force Capacity 4.5 ton

Die Type W Die and X Die

EU RoHS Indicator Yes
Sub Brand HYTOOL

Tool Type Hand Operated Crimper

 Trade Name
 HYTOOL™

 UPC
 781810446003

 UPC 12 Digit
 78181044600333

Dimensions

Length25.38 inWeight6.25 lbWidth7.04 in

Conductor Related

Crimping Ranges Copper: 10 sol. - 500 Kcmil; Copper Flex: #8 to 350 kcmil

Certifications and Compliance

Standards - RoHS Compliance EX

Status

Logistics

Minimum Pack Quantity

Package Contents Tool only

Product Assets

Catalogs - Full Line BURNDY Catalog Customer Notices - Prop 65 Notice

Installation Manuals -

BUR_464750_MD6_MD66_MD637_MD638

Sales Drawings - 2240

