

Dieless Mechanical Crimper, #8 Str - 250 kcmil Copper Code, #8 Str - 4/0 Str Aluminum Code, 30 Navy - 250 Navy Copper Navy Cable

By Burndy Catalog # MY293

Dieless Crimper, #8 Str-250 kcmil CU Code, #8 Str-4/0 Str AL Code, 30-250 Navy CU Navy Cable.

Features

- Two-ply covered handles on MY29-3C and MY29-11C designs
- Heavy duty forged steel back, body and handles
- Strong reinforced forged steel back
- .31" dia. hole for bench mounting operations
- Comfort grips
- Extra strong, heavy reinforced handles
- · Indentor die
- · Knurled steel adjusting knob

Application

Crimping

General

Application - For Use On #8-250 kcmil CU Code, 30

Navy-250 Navy CU Navy Cable, #8-4/0 AL Code

Die Type Dieless EU RoHS Indicator Yes

Finish Type Black Matte
Sub Brand HYTOOL

Tool Type Mechanical Dieless Crimper

 Trade Name
 HYTOOL™

 UPC
 781810462003

 UPC 12 Digit
 7818104620033



Dimensions

Dimensions 22.65 in x 4.86 in x 1.12 in

Height 1.12 in
Length 22.65 in
Weight 8 lb
Width 4.86 in

Conductor Related

Crimping Ranges #8 Str. - 250 kcmil, 30 Navy -

250 Navy, #8 Str. - 4/0 Str

Certifications and Compliance

Standards - RoHS Compliance EX Status

Logistics

Minimum Pack Quantity

Package Contents Tool only

Product Assets

Catalogs - Full Line BURNDY Catalog Customer Notices - Prop 65 Notice Sales Drawings - sd026316-01

