



# Stainless Steel Circular Non-Butting Twin U Die, 750 kcmil, 600 Flex, Black, Index 24

By Burndy  
Catalog # [U39RT](#)

Non-Butting U Die, 750 kcmil, 600 Flex, Black, Index 24.



## Application

Crimping

## General

|                              |   |
|------------------------------|---|
| Application - For Use On     | Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter |
| Color Code                   | Black   |
| Construction Material - Main | Stainless Steel   |
| Crimp Force Capacity         | 12 ton  |
| Die Index                    | 24  |
| Die Type                     | U Die   |
| EU RoHS Indicator            | Yes   |
| Sub Brand                    | U-DIE   |
| Type                         | Die   |
| UPC                          | 781810627433  |
| UPC 12 Digit                 | 7818106274333   |

## Dimensions

|                        |         |
|------------------------|---------|
| Dimension - Width inch | 1.38    |
| Dimension - Width mm   | 35      |
| Weight                 | 0.26 lb |

## Conductor Related

Crimping Ranges 750 Kcmil/600 Flex

## Certifications and Compliance

Standards - RoHS Compliance EX Status

## Logistics

|                       |          |
|-----------------------|----------|
| Carton Quantity       | 1        |
| Minimum Pack Quantity | 1        |
| Package Contents      | Die only |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10102827](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-U39RT-SPEC-EN | REV 5/2023