



Plier-style Crimper/Cutter, Installs #22 AWG - #10 AWG Bare and Nylon Insulated Connectors; Cuts Aluminum and Copper

By Burndy
Catalog # [Y10D](#)

Plier-style Crimper/Cutter for #22-10 AWG Bare and Nylon Connectors; Cuts CU/AL.



Features

- One tool for both nylon insulated and bare connectors
- Precision machined wire cutter for aluminum and copper
- Heavy duty forged steel, rust resistant finish

Application

Crimping and Cutting

General

| | |
|------------------------------|--|
| Application - For Use On | #22-10 AWG Insulated and Uninsulated Terminals and Splices |
| Construction Material - Main | Steel Alloy |
| Die Type | Permanent Die Grooves |
| EU RoHS Indicator | Yes |
| Sub Brand | HYTOOL |
| Tool Type | Plier Hand-held Tool |
| Trade Name | HYTOOL™ |
| Type | Crimper and Cutter |
| UPC | 781810700860 |

Dimensions

Length 9.75 in

Conductor Related

Crimping Ranges Copper: #22 AWG - #10 AWG

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - BUR_476021_SOMI_Y10D and Y1022](#)
[Sales Drawings - sd211531-01](#)
[Video - Small Terminal Tools\(Y10 & MRE\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-Y10D-SPEC-EN | REV 5/2023