



Ratchet Cable Cutter, Cuts up to 336 kcmil ACSR, up to 500 kcmil Aluminum, up to 350 kcmil Copper

By Burndy
Catalog # [RCC336](#)



Ratchet Cable Cutter, Cuts up to 336 kcmil ACSR, 500 kcmil AL, 350 kcmil CU.

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable
EU RoHS Indicator	Yes
Sub Brand	RATCHET CUTTER
Tool Type	Ratchet Cable Cutter
Type	Cutter
UPC	781810459980
UPC 12 Digit	7818104599800

Dimensions

Cable Insulation Diameter Maximum	1.250 in
Length	10.5 in
Weight	1.2 lb
Width	1.25 in

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Cutters \(2150\)](#)
[Sales Drawings - 10082457](#)



A proud member of the Hubbell Family.