

# Hard Disk Drives (Enterprise and Non-Enterprise)

For Use with EVS Storage Units, Dahua NVRs, and HDCVI DVRs

### **Enterprise HDDs**

- 8 TB or 10 TB Capacity
- 3.5-in. Enterprise Drive for Bulk Data Applications
- RAID Support
- Designed for 24/7 Security-optimized Hard Drive Applications
- Tarnish-resistant Components to Minimize Environmental Effects

## **Enterprise HDDs**

Technical Specification

	DHHDDB8T	DHHDDB10T		
Capacity	8 TB	10 TB		
Spindle Speed	7200 RPM	7200 RPM		
Cache, multi-segmented	256 MB	256 MB		
Interface Access Speed	6.0 Gb/s, 3.0 Gb/s, 1.5 Gb/s	6.0 Gb/s, 3.0 Gb/s		
Bytes per Sector	512	512		
Maximum Sustained Transfer Rate	249 MB/s	245 MB/s		
Average Latency (ms)	4.16 ms	4.16		
Average Idle Power	7.64 W	5.0 W		
Average Operating Power	12.81 W	9.5 W		
MTBF Hours	2 million	2.5 million		
Power Supply Requirements	+12 V and +5 V	+12 V and +5 V		
Operating Temperature	5 °C to 60 °C (41 °F to 140 °F)	5 °C to 60 °C (41 °F to 140 °F)		
Weight	716.0 g (1.58 lb)	670.0 g (1.48 lb)		
Dimensions (H x W x D)	26.11 mm x 101.85 mm x 147.0 mm (1.03 in. x 4.01 in. x 5.79 in.)	26.11 mm x 101.85 mm x 147.0 mm (1.03 in. x 4.01 in. x 5.79 in.)		

#### Non-enterprise HDDs

- Designed for 24/7 Security-optimized Hard Drive Applications
- Engineered for Workloads up to 180 TB/year
- Capacity Up to 10 TB, Supports 64 Cameras per Drive
- Low Power Consumption and Startup Current
- Tarnish-resistant Components to Minimize Environmental Effects

## Non-enterprise HDDs

#### **Technical Specification**

	DHHDDA1T	DHHDDA2T	DHHDDA3T	DHHDDA4T	DHHDDA6T	DHHDDA8T	DHHDDA10T
Capacity	1 TB	2 TB	3 TB	4 TB	6 TB	8 TB	10 TB
Interface	SATA 6 GB/s						
Cameras Supported	up to 64						
Cache	64 MB	256 MB	256 MB	256 MB	256 MB	256 MB	256 MB
Maximum Sustained Transfer Rate	180 MB/s	235 MB/s	245 MB/s				
Startup Current, (typical at 12 V)	1.8 A	2.0 A					
Average Operating Power	5.6 W	3.7 W	5.6 W	3.7 W	5.0 W	8.73 W	10.1 W
Average Idle Power	4.0 W	2.5 W	4.0 W	2.5 W	3.4 W	7.5 W	7.8 W
Operating Temperature	0° C to 70° C (32° F to 158° F)	0° C to 70° C (32° F to 158° F)	0° C to 70° C (32° F to 158° F)	0° C to 65° C (32 °F to 149 °F)	0° C to 70° C (32° F to 158° F)	5° C to 70° C (41° F to 158° F)	0° C to 65° C (32° F to 149° F)
Non-operating Temperature	–40° C to 70° C (–40° F to 158° F)	–40° C to 70° C (–40° F to 158° F)	–40° C to 70° C (–40° F to 158° F)	–40 °C to 65 °C (–40 °F to 149 °F)	–40° C to 70° C (–40° F to 158° F)	–40° C to 70° C (–40° F to 158° F)	–40° C to 65° C (–40° F to 149° F)
Weight	415.0 g (0.915 lb)	415.0 g (0.915 lb)	490.0 g (1.08 lb)	490.0 g (1.08 lb)	610.0 g (1.345 lb)	716.0 g (1.58 lb)	690.0 g (1.52 lb)
Dimensions, mm (in.) (H x W x D)	20.20 x 101.85 x 146.99 (0.80 x 4.0 x 5.79)	20.20 x 101.85 x 146.99 (0.80 x 4.0 x 5.79)	20.20 x 101.85 x 146.99 (0.80 x 4.0 x 5.79)	20.20 x 101.85 x 146.99 (0.80 x 4.0 x 5.79)	26.11 x 101.85 x 146.99 (1.03 x 4.0 x 5.79)	26.11 x 101.85 x 146.99 (1.03 x 4.0 x 5.79)	26.11 x 101.85 x 146.99 (1.03 x 4.0 x 5.79)