

Data Sheet | Item Number: 2009-615

WMB-Inline; for Smart Printer; 1200 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

<https://www.wago.com/2009-615>



Color: ■ white

Similar to illustration

Technical data

Suitable	for Weidmüller's rail-mount terminal blocks; replaces WS 10/5 marker
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	1,200 WMB markers (5 mm)/reel
Properties	for Weidmüller rail-mount terminal blocks; replaces WS 10/5 marker
Flammability class per UL94	V2
Printing device	Smart Printer (thermal transfer printer)

Physical data

Marker/strip width	5 ... 5.2 mm
Marker width	5 mm

Mechanical data

Smear resistance	in conjunction with 258-5005 Ink Ribbon
------------------	---

Material data

Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	114.7 g
Fire load	2.34 MJ

Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 8.0	EC000761
ETIM 7.0	EC000761
PU (SPU)	1 pcs
Packaging type	Bag
Country of origin	DE
GTIN	4050821659662
Customs tariff number	39269097900