

Data Sheet | Item Number: 258-5001

Thermal transfer printer; Smart Printer; for complete control cabinet marking; Without marking material

<https://www.wago.com/258-5001>



This item includes:



Item No.: 258-5005

1

Thermal transfer ink ribbon; for Smart Printer; black

Item No.: 258-5006

1

Roller; for Smart Printer; for marking strips, device and equipment markers, conductor and cable markers

Item No.: 258-5007

1

Roller; for Smart Printer; for WMB-Inline WAGO (2009-115, -114, -113); 1 grinding device

System requirements

Memory	4 GB
Supported operating systems	Windows 7 Windows 8 Windows 10

Technical data

Marking method	Thermal transfer
Print head	Glass layer, spring-mounted
Print resolution	300 dpi 300 dpi (12 pixels/mm)
Print speed	Max. 127 mm/s (WAGO recommends 50.8 mm/s)
Recommended print speed	50 mm/s
Print speed (max.)	127 mm/s
Print width	47 mm
Print length (max.)	762 mm
See-through/reflective sensor	Yes, centrally mounted
Memory	8 MB
Marking software	Smart Script
Interfaces	USB, RS-232, ETHERNET 10/100 Mbps
Operating voltage	100 ... 240 VAC, 50 ... 60 Hz (automatic adjustment)
Safety approvals	CE (EMC)
Operating display	Color TFT LCD with navigation button
Ink ribbon	External roll diameter: 40 mm; Internal core diameter: 12.7 mm (0.5 inch); Max. length: 110 m; Max. width: 58 mm
Ink ribbon width	46 mm / 1.811 inches
Ink ribbon length	74 m / 360.9
Ink ribbon external roll diameter	33 mm / 1.299 inches
Ink ribbon internal core diameter	12.5 mm / 0.492 inches

Technical data

Scope of delivery	Power supply + cable, 2 rollers (258-5006 + 258-5007), 1 roll holder, 1 ink ribbon (258-5005), Smart Script marking software and driver, USB cable, external unwinder, 2 empty cardboard roller cores
-------------------	---

Physical data

Height	175 mm / 6.89 inches
Width	135 mm / 5.315 inches
Depth	245 mm / 9.646 inches

Material data

Weight	3467 g
Fire load	0 MJ

Environmental requirements

Ambient temperature (storage)	-20 ... +50 °C
Ambient temperature (operation)	+5 ... +40 °C

Commercial data

ETIM 8.0	EC000610
ETIM 7.0	EC000610
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	TW
GTIN	4066966148145
Customs tariff number	84433210000