# Eaton LS-S11S

# Catalog Number: LS-S11S

Eaton Eaton Safety Switch Body, LS-Titan, Screw Terminals, 6A at 230 Vac, 3A at 24 Vdc, Plus or minus 0.02mm, 99.97 cm/sec, 1NO-1NC with positive opening contact

## General specifications

Product Name Catalog Number Eaton LS-Titan miniature DIN limit switch LS-S11S

UPC 786685392486

Product Height .1 in

Product Weight

.12 lb

Compliances RoHS Compliant

Catalog Notes

0



Product Length/Depth 2.99 in

Product Width 1.22 in

Warranty

1 year

Certifications UL Listed

## Product specifications

#### Contact configuration

1 NO-1 NC with positive opening contact

Operating temperature - min

-13 °F

#### Maximum AC current

6 A at 230 Vac

#### Maximum DC current

3 A at 24 Vdc

Connection

Screw terminal

Enclosure material

Plastic

#### Series

LS-Titan

Туре

LS-Titan

## Accuracy

±0.02mm

Contact Rating 6A at 230 Vac, 3A at 24 Vdc

Operating temperature - max 158 °F

Operating speed 99.97 cm/sec

Environmental rating

IP66, IP67

## Resources

Brochures

LS-Titan Safety Limit Switches

Catalogs Eaton's Volume 8—Sensing Solutions

#### Specifications and datasheets

Eaton Specification Sheet - LS-S11S



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2023 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia