



# A-Shape LED

## 8.5A19/LED/950/FR/P/ND 4/1FB

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.


### Product data

General Information		Warm-up time to 60% light	
Cap-Base	E26 [Single Contact Medium Screw]		0.5 s
Nominal lifetime	11,000 hour(s)	Power Factor (Fraction)	0.5
Switching Cycle	50,000	Voltage (Nom)	120 V
Lighting Technology	LED	<b>Temperature</b>	
<b>Light Technical</b>		T-Case Maximum (Nom)	85 °C
Color Code	950 [CCT of 5000K]	<b>Controls and Dimming</b>	
Beam Angle (Nom)	150 degree(s)	Dimmable	No
Luminous Flux	800 lumen	<b>Mechanical and Housing</b>	
Color Designation	Daylight	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	5000 K	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	94.00 lm/W	Bulb Shape	A19 [A 19mm]
Color Consistency	<6	<b>Approval and Application</b>	
Color rendering index (CRI)	90	Energy Certifications	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	EU RoHS compliant	Yes
<b>Operating and Electrical</b>		<b>Product Data</b>	
Line Frequency	60 Hz	Order product name	8.5A19/LED/950/FR/P/ND 4/1FB
Input Frequency	60 Hz	Order code	565135
Power Consumption	8.5 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	135 mA	Numerator - Packs per outer box	4
Wattage Equivalent	60 W		
Starting Time (Nom)	0.5 s		

# A-Shape LED



Material number (12NC)	929003005004
Full product name	8.5A19/LED/950/FR/P/ND 4/1FB
EAN/UPC - Case	50046677565133

## Dimensional drawing




Product	D	C
8.5A19/LED/950/FR/P/ND 4/1FB	60 mm	104 mm

## Photometric data



General uniform lighting - 8.5A19/LED/950/FR/P/ND 4/1FB



Light Distribution Diagram - 8.5A19/LED/950/FR/P/ND 4/1FB



Spectral Power Distribution Colour - 8.5A19/LED/950/FR/P/ND 4/1FB

# A-Shape LED

## Lifetime



Lumen Maintenance Diagram - 8.5A19/LED/950/FR/P/ND 4/1FB

Life Expectancy Diagram - 8.5A19/LED/950/FR/P/ND 4/1FB

