

Mercmaster™ LED Low Profile Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:

Class I, Division 2, Groups A,B,C,D
 Class I, Zone 2, AEx ec IIC
 Zone 21, AEx tb IIIC
 Class I, Zone 2 Ex ec II
 Class II, Division 1, Groups E,F,G
 Zone 20, Group IIIC
 Class II, Division 2, Groups F,G
 Class III

NEC/CEC:

Type 3R, 4, 4X
 IP66/IP67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water) ⌘
 American Bureau of Shipping (ABS) Certified
 International Dark Sky (IDA) Approved















ATEX:

Zone 2 and 21-22
 II 2 D
 II 3 GD
 IP66
 IK08

IECEX:

Zone 2 and 21-22
 Ex ec IIC
 Ex op is tb IIIC
 Ex tc IIIC
 IP66
 IK08

Replacement Parts

		Description	Catalog Number
Globes and Gaskets			
		Clear Globe (polycarbonate)	VPGL-LED
		Diffused Globe (polycarbonate)	VPGL-DIFF
		Glass Globe	VPGL-GLASS
		Light Distribution	Catalog Number
Closed Prismatic Glass Refractors – All Heat-Resistant			
		NEMA Type V	LPG-R5S
		Glass Refractor ①	
Accessories			
		Description	Catalog Number
Reflector and Large Refractor			
		30° Angle White Polyester Reflectors	CMR-4AN
30° Angle	Large Refractor	NEMA Type V Large Glass Refractor	LPG-R5
Guards			
			
Glass Globe Guard	Refractor Guard	Large Refractor Guard	
		Glass Globe Guard	MGU1
		Refractor Guard for LPG-R5S	KRG2S
		Large Refractor Guard for LPG-R5	KRG2
Safety Cable			
		Stainless steel	LEDSC
Visor			
		Electrostatically applied gray epoxy powder coat finish on Aluminum Visor	MMVISOR
Mounting Hood Adapters			
	Manufacturer	Installed Mounting Hood	Appleton Adapter Catalog Number
	Crouse-Hinds™ Champ®	APM2/3 - Pendant CM2/3 - Ceiling HPM2 - Flexible Pendant	MMADCHVS
	Appleton™ Mercmaster™ II	LPA75/100 - Pendant LPC75/100 - Ceiling	MMADIIS
	Crouse-Hinds™ Champ®	TWM2/3 - Wall JM5 - 25° Angle Stanchion PM5 - 90° Straight Stanchion	MMADCHVA
	Appleton™ Mercmaster™ II	LPWB75, LPWB100 - Wall LPS125, LPS150 - 25° Angle Stanchion	MMADIIA
	Killark™	VMX2B, VMX3B, VMX6B, VMX7B, VMX9B - Ceiling VMA2B, VMA3B - Pendant VMD4B, VMD5B, VMS4B, VMS5B - Stanchion VMB2B, VMB3B - Wall VMC2B, VMC3B - Pendant Cone	MMADKVA

① NEMA Type V refractor only permitted for cCSAus rating.

⌘ Use of fuse voids Marine Outside Type (Salt Water) rating.