



LED Post Top (PT)

PT50-WW-G1-T2-3-HV3-FAWS-TLRPC-BK

Post Top LED, Warm White, Generation 1, tenon mount, Type 5, Field Adjustable Wattage Selector - 92 lm/W

The KEENE LED post top is compact and comfortable, with a sleek low profile design suitable for 10'-16' mounting heights. Features include low glare comfort optics, field adjustable output, twist lock receptacle with shorting cap, and an LED driver suitable for 120 volt through to 347 volt operation. The comfortable, low glare optics make this an ideal choice for pedestrian scale applications such as condominiums, hotel parking lots, parks and walkways.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	3000 K
CRI	70
Photometric Distribution Type	Type III
Mounting	Pole Top
Number Of Pieces	1
Operating and electrical	
Voltages	120/277/347 V
Luminaire Input Watts	22 32 46 53 W
Mechanical and housing	
Enclosure	Metal and Plastic
Initial performance (IEC compliant)	
Luminaire Lumens	2000 3300 4200 4900 lm

Efficacy	92 lm/W
Product data	
Order product name	PT50-WW-G1-T2-3-HV3-FAWS-TLRPC-BK
EAN/UPC - Product	783352026064
Order code	912401482237
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401482237
Catalog Number	PT50-WW-G1-T2-3-HV3-FAWS-TLRPC-BK
Catalog Number Description	Post Top LED, Warm White, Generation 1, tenon mount, Type 5, Field Adjustable Wattage Selector