

# Data Sheet | Item Number: 2004-405

Jumper; 5-way; insulated; light gray

<https://www.wago.com/2004-405>



Color: ■ light gray

Similar to illustration

## Electrical data

### Ratings per IEC/EN

|                         |       |
|-------------------------|-------|
| Nominal voltage (III/3) | 800 V |
| Rated current           | 32 A  |

### Ex information

|                         |      |
|-------------------------|------|
| Rated current (Ex e II) | 30 A |
|-------------------------|------|

## Physical data

|                   |                       |
|-------------------|-----------------------|
| Width             | 29 mm / 1.142 inches  |
| Height            | 4.1 mm / 0.161 inches |
| Depth             | 19 mm / 0.748 inches  |
| Jumper assignment | 1-2-3-4-5             |

## Material data

Note (material data)

[Information on material specifications can be found here](#)

|           |            |
|-----------|------------|
| Color     | light gray |
| Fire load | 0.019 MJ   |
| Weight    | 3.7 g      |

## Commercial data

|                       |               |
|-----------------------|---------------|
| Product Group         | 22 (TOPJOB S) |
| eCl@ss 10.0           | 27-14-11-40   |
| eCl@ss 9.0            | 27-14-11-40   |
| ETIM 8.0              | EC000489      |
| ETIM 7.0              | EC000489      |
| PU (SPU)              | 25 pcs        |
| Packaging type        | Bag           |
| Country of origin     | DE            |
| GTIN                  | 4055143699891 |
| Customs tariff number | 85366990990   |

**Environmental Product Compliance**

RoHS Compliance Status

Compliant, No Exemption

**Approvals / Certificates**

**Declarations of conformity and manufacturer's declarations**



| Approval                      | Standard | Certificate Name |
|-------------------------------|----------|------------------|
| Railway<br>WAGO GmbH & Co. KG | -        | Railway Ready    |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)