

Eaton TRUSBAC20W-BOX

Catalog Number: TRUSBAC20W-BOX

Eaton Combination USB Type AandC Charger, 20A 5-20R Receptacle, White, USB, Brass, Thermoplastic, Flush, Two-pole, Three-wire, Tamper resistant, Decorator, 125V

General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton combination USB charger with duplex receptacle | TRUSBAC20W-BOX |
| | UPC |
| | 032664755941 |
| Product Length/Depth | Product Height |
| 1.67 in | 4.19 in |
| Product Width | Product Weight |
| 1.3 in | .285 lb |
| Warranty | Certifications |
| 1 year | NOM |
| | cULus Listed |



Product specifications

Color

White

Wiring method

Screw terminals

Features

Tamper resistant

5A Charging

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#12-14 AWG

Combination type

USB

Amperage Rating

20 A

Number Of Poles

Two-pole

Contact material

Brass

Type

Type AC

NEMA configuration

5-20R

Design type

Receptacle

Style

Decorator

Number of wires

Three-wire

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125 V

Resources

Multimedia

[Eaton's USB charging receptacles - Never miss a moment](#)

[Introduction to USB-C Duplex Receptacles](#)

[Eaton USB Charging Receptacles](#)

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

Specifications and datasheets

[USB-AC charger TR receptacle spec sheet](#)

Torque rating

14 lbf-inch

Packaging type

Retail Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)