



Compression Terminal

By Burndy
Catalog # [YAV102TC14](#)

Copper Compression Lug, 2 Hole w/ Inspection Window, 14 AWG -10 AWG (str)/ 12 AWG-10 AWG (sol), 1/4" Stud, 5/8" Stud Hole Spacing, Short Barrel, Tin - Electro Plated.



General

EU RoHS Indicator	Yes
Physical Attribute - Number of Holes	2
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021842

Dimensions

Dimension - D inch	1.14 in
Dimension - N inch	0.31 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper Solid Size Range	12 -10 Sol
Conductor - Copper Str Navy Size Range	3 (7) Navy-9 (37) Navy
Conductor - Copper Str Size Range	14 AWG - 10 AWG

Certifications and Compliance

Certification - UL Recognized	No
Industry Standard(s)	UL 486A-486B

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YAV102TC14_MODEL-STEP](#)
[3D Models - YAV102TC14_MODEL-IGES](#)
[3D Models - YAV102TC14_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SD035209-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV102TC14-SPEC-EN | REV 6/2023