



YA26A3, 2/0 AWG, AL, 2 Hole, 1/2" Stud 1-3/4" Hole Spacing, AL9CU

By Burndy
Catalog # [YA26A3](#)

AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.



Application

Wire Termination

General

Color Code	Olive
Connector Type	DUAL RATED
Die Index	297
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	ALUMINUM
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A
UPC	781810753507
UPC 12 Digit	7818107535077

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.17 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.11 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	121 mm
Dimension - Length Overall inch	4.78 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1-3/8

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE
Wire Size	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Aluminum Installation Instructions](#)
[Sales Drawings - SD073935-01](#)

Dimension - Stud Size fraction 1/2
Dimension - Stud Size inch 1/2
Dimension - Thread Size 1/2
Dimension - Z inch 0.73 in
Physical Attribute - Tongue Straight
Angle



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA26A3-SPEC-EN | REV 6/2023