



# Compression Splice

By Burndy  
Catalog # [YS4CA1](#)



AL Splice, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13 oxide inhibitor, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

## Application

Wire Splice

## General

Color Code	Green
Connector Type	DUAL RATED
Die Index	375
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	ALUMINUM
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Temperature Rating	194
Trade Name	HYLINK™
Type	YS-A, Standard Barrel
UPC	781810756706
UPC 12 Digit	7818107567066

## Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.86 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Outside Diameter inch	0.43 in
Dimension - Strip Length inch Length	1.0 in 1.97 in
Outside Diameter	0.43 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor - Copper Str Compact Size	4
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	4 AWG
Conductor Type	CODE
Wire Size	4 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1

## Product Assets

- [3D Models - YS4CA1\\_MODEL-STEP](#)
- [3D Models - YS4CA1\\_MODEL-IGES](#)
- [3D Models - YS4CA1\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - SD..073942-01](#)



A proud member of the Hubbell Family.

