

Compression Terminal

By Burndy Catalog # YAL26T38

Copper HYLUG™, Single Hole w/ Inspection Window, 2/0 AWG, 3/8" Stud,13 index,Black, Short Barrel,Electro- Tin Plated.



Application

Wire Termination

General

Color Code Black

Connector Type STANDARD BARREL

Construction Material - Main Copper Die Index

Contact Manufacturer **EU RoHS Indicator**

Feature - Barrel Style Chamfered Feature - Barrel Type Standard

Finish Type Electro Tin plated

Material COPPER

Physical Attribute - Number of 1

Holes

Physical Attribute - Tongue Standard

Type

Plated

Plating Type Tin - Electro Plated

Sub Brand **HYLUG** Trade Name HYLUG™

Type Standard Barrel, Tin Plated

56 mm

2.19 in

UPC 781810416990

Dimensions

Dimension - B Length inch 0.94 in Dimension - Bolt Hole Size 0.39 in

inch

Dimension - Bolt Size fraction 3/8 0.38 Dimension - Bolt Size inch Dimension - D inch 0.83 in Dimension - Hole Size fraction 3/8 Dimension - Hole Size inch 0.41 Dimension - Hole Size mm 10.4 mm

Dimension - L Length Overall

mm

Dimension - Length Overall inch

Dimension - N inch

0.41 in Dimension - Outside Diameter 0.56 in inch

Dimension - Pad Width inch 0.83 in Dimension - Stud Size fraction 3/8 Dimension - Stud Size inch 3/8

Physical Attribute - Tongue Straight

Electrical Ratings

Voltage - Maximum 35000 Voltage Rating 35 kV

Conductor Related

Conductor - Copper Str Size 2/0 AWG Conductor - Copper Str Size 2/0 AWG Range

Conductor - Material **COPPER** Conductor Size 2/0 AWG Conductor Type CODE

Certifications and Compliance

Certification - CSA Approved Yes Certification - ETL No Certification - UL Recognized No Certification - cULus

Industry Standard(s) UL 486A-486B

Standards - RoHS Compliance CM

Status

UL Listed Yes

Logistics

Carton Quantity 10 Minimum Pack Quantity

Product Assets

Customer Notices - Prop 65 Notice Sales Drawings - CSD029213



A proud member of the Hubbell Family.