


Landscape

## Accent





## BL5016 Accent Aluminum



Project:		
Location:		
Cat.No:		
Туре:		
Lamps:	Qty:	
Notes:		

# Ordering guide

Example: BL5016HS7LED7	NFW
------------------------	-----

Series	Finish	Mount	Lamp	Optics	ССТ
BL5016		S7	LED7		W
BL5016 Aluminum Bullyte	A Black H Bronze	<b>S7</b> Stake	LED7 7W LED	FL Flood NF Narrow Flood	W Warm

Fixture will be shipped with lamp. Lamp not sold separately.

## **Specifications**

#### Features

- 12 Volt
- MR16 LED Lamp
- 1/2" NPS fitter
- Ships with S7 mounting stake

#### LED

- 460 lumens (dimmable)
- 25,000 hour life (no mercury)
- 7W lamp with 24° or 36° beam spread
- Color temperature (CCT): warm white (3,000K nominal)
- Lamp only sold integral to BL5016

#### Housing

Die-cast marine grade aluminum alloy with fully-adjustable swivel arm and vibration-proof locking teeth. 1/2" NPS male threads to screw onto accessory mounting stake or junction box (sold separately). Gasketing is silicone and fasteners are 300 series stainless steel.

#### Shroud

Fully-rotatable, double gasketed, die-cast marine grade aluminum alloy.

#### Finish

Thermoset powder coated in; black, bronze, or hand-rubbed verde antiqued over black. Electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

#### Optics

Clear tempered glass, affixed at 10° angle for natural cleaning.

#### Wiring

This 12 Volt fixture is pre-wired with a 3 ft. pigtail of 18-2 AWG,  $105^{\circ}$  C, SPT-1W wire for easy hookup to the low voltage supply cable. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable (not included). 12 Volt system requires remote transformer (not included).

#### Socket

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. Stainless steel retention clip affixed to socket to securely hold lamp in place.

#### Labels

ETL and cETL listed. 5-year limited warranty.

# Signify

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 800-555-0050 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owner