


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: B1 A

Product Code	B1	Aluminum Bullyte
Finish	A H G	Black Bronze Verde

Specifications

HOUSING:

Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately. Gasketing is silicone. Fasteners are 300 series stainless steel. Shroud is optional.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Provided with optional shrouds only.

LAMPING:

100W maximum PAR20/R20 medium base lamp. Incandescent lamp is not included. Lower wattage lamps are acceptable. (Note: If HID or R lamp is used, accessory shroud must also be used.)

ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact. Fixture is pre-wired with 18 AWG black, white, and ground wires.

BALLAST:

Must order inground (IBH) or above ground (ABH) ballast housing separately.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width: 3 7/8" (98mm) **Length:** 8 1/2" (216mm) **Max. Weight:** 1.4 lb.

