



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Reflector Trim		Frame-in Kit (Incandescent)		Lamp	Voltage
513ABX	Antique Brass Plated	Remodeler Non-IC	501X	50W PAR20	120V
513BKX	Black Paint	Frame Non-IC	502X	50W PAR20	120V
513STX	Stainless Steel Plated	Lytening Frame AirSeal®	502AICSX	50W PAR20	120V
513WHX	White Paint				

Frame-in Kit (HID)		Lamp	Voltage
Remodeler Non-IC	501MH39P20E1	39W PAR20 CMH	120V
Frame Non-IC	502MH39P20E1	39W PAR20 CMH	120V

### Features

**Housing** : 25ga galvanized steel.

**Residence Mounting Clips**: Factory-installed; zinc plated spring steel; free-hand installation.

**Flange Housing**: Cold rolled steel 22ga.

**Adjustable Lampholder Support**: 27ga. steel, rotates 358° horizontally and 0° to 30° vertically.

**Mounting Clips (2)**: 28ga. Stainless steel spring.

### Frame-in Kit

See Frame-In Kit specification sheets for more details. appropriées.

### Accessories

500SQBK

Black Square Plate

500SQWH

White Square Plate

### Marking

cCSAus Certified, suitable for damp locations

