



LED PAR30 S/L

8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Lighting Technology	LED
Switching Cycle	50,000
Nominal lifetime	25,000 hour(s)
Cap-Base	E26 [Single Contact Medium Screw]
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	800 lumen
Luminous Intensity (Nom)	1,600 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	94.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8.5 W
Lamp Current (Nom)	80 mA
Wattage Equivalent	75 W


Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Certifications	Energy Star
EU RoHS compliant	Yes
Product Data	
Order product name	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB

LED PAR30 S/L

Order code	568030
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material number (12NC)	929003028004
Full product name	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB



EAN/UPC - Case	50046677568035
----------------	----------------

Dimensional drawing



Product	D	C
8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	94 mm	90 mm


Photometric data



© 2023 Philips Lighting B.V. All rights reserved. Page 10

Spectral Power Distribution Colour - 8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB


Accent Lighting Spots - 8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB



Light Distribution Diagram - 8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 8.5PAR30S/LED/927/F40/DIM/GULW/T20
6/1FB

Lumen Maintenance Diagram - 8.5PAR30S/LED/927/F40/DIM/GULW/T20
6/1FB

