

# PHILIPS

Bulb (Dimmable)

LED

8W-60W

E26

Warm Glow

Dimming

046677574888



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 10.5 cm
- Weight: 0.033 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 300 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 95
- Color temperature: 2700-2200 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 927-922 | CCT of 2700K-2200K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 85 mA
- Efficacy: 100 lm/W

## Packaging information

- EAN: 046677574888
- EOC: 574889
- Product title: 8A19/PER/UD/FR/G/E26/WGD 4/3PFT20

#### Power consumption

- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8 W
- Wattage equivalent: 60 W

#### Product dimensions and weight

- Length: 10.5 cm

#### Rated values

- Rated beam angle: 300 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8 W

#### Technical specifications

- Frequency: 60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 046677574888
- Net weight: 0.090 kg
- Gross weight: 0.152 kg
- Height: 14.600 cm
- Length: 6.500 cm
- Width: 18.500 cm
- Material number (12NC):  
929003083235



Issue date: 2023-05-26  
Version: 0.51

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)