



# Energy Saver T2

## EL/mdTQS 23W T2

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years\* reducing the hassle of frequent replacements.

### Product data




General Information	
Lighting Technology	Compact Fluorescent Integrated
Switching Cycle	5,000
Rated Lifetime (Hours)	10,000 hour(s)
Nominal lifetime	10,000 hour(s)
Cap-Base	E26 [Single Contact Medium Screw]
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,600 lumen
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	67 lm/W
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	23.0 W
Lamp Current (Nom)	360 mA
Power Factor (Fraction)	0.55

Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	2 mg
Energy Consumption kWh/1000 h	23 kWh

Product Data	
Order product name	EL/mdTQ 23W T2
Order code	414011
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material number (12NC)	929689749901
Full product name	EL/mdTQS 23W T2
EAN/UPC - Case	50046677414011

# Energy Saver T2

## Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQ 23W T2	61.5 mm	115.3 mm	50.5 mm

Product
EL/mdTQ 23W T2

Product
EL/mdTQ 23W T2

